




QPG6100


Zigbee / Thread / Bluetooth® Low Energy Smart Home Communications Controller

Product Brief

The QPG6100 is a multi-standard Smart Home Communications Controller featuring Dynamic Multi-Protocol and ConcurrentConnect™ technology. This enables Zigbee, Thread and Bluetooth® Low Energy to operate simultaneously in a single chip design.



- Dynamic Multi-Protocol and ConcurrentConnect™ technology allows concurrent listening and instantaneous switching between Bluetooth Low Energy and IEEE 802.15.4 protocols with no observable blind spots
- Simplify Gateway dependencies by bridging Zigbee, Thread and Bluetooth Low Energy Mesh networks
- Enhanced security capabilities ensure inherent highly secure smart home solution with built in support for secure boot and OTA software upgrade
- Simple and compact solution requires minimal board space
- Patented IEEE 802.15.4 antenna diversity scheme enables increased effective range
- Designed for low power IoT end node applications such as:
 - Connected Lighting
 - Sensors
 - Smart Plugs
 - Thermostats
 - Smart Meters



Key Features

- Operates in the worldwide 2.4 GHz ISM-band
- Integrated baluns and RF filters
- Support for external LNA and/or PA
- IEEE 802.15.4 compliant PHY and Real-Time MAC
 - Preamble-based antenna diversity
 - Packet-in-Packet resynchronization
 - Multi-Stack / Multi-Channel support, operating in up to 3 PANs on different channels
- Bluetooth v 5.1 compliant Low Energy Controller
 - High Data Rate (2 Mbits/s)
 - Long Range Coded PHY
 - Link layer security
 - Advertising extensions
 - Mesh
 - Support for Angle of Arrival and Angle of Departure
- ConcurrentConnect technology**
 - Concurrent IEEE 802.15.4 and Bluetooth listening
 - Allows combining Bluetooth Low Energy Central/Observer or Mesh Node with Zigbee/Thread router
- Advanced Security Engine
 - Hardware accelerated AES and CCM* encryption with 128, 192 and 256-bit keys
 - Hashing engine: SHA-128, SHA-2 (SHA-256, SHA-512)
 - Public Key Crypto
 - Elliptic Curve; support for ECDSA, ECDH, P256, Curve25519, J-Pake, ECMQV, EdDSA, etc.
 - Cryptographic Random Number Generator
 - Support for Physical Unclonable Function (PUF)
- Arm® Cortex®-M4 processor with DSP functionality, executing code from Flash or RAM at up to 64 MHz clock speed.
- 512 Kbyte Flash Program memory; patchable ROM
- 96 Kbyte Low Leakage Retention RAM
- Full internal IO pull-up / pull-down support during active and standby states
- Fast and low-power analog measurements
- Wake Up on RF pattern

Excellent Range and Reliability

The QPG6100 has been optimized for reliable communication in harsh radio environments. Built-in IEEE 802.15.4 antenna diversity with two antennas improves the reliable link budget by 8 dB resulting in approximately 70% more reliable range compared to similar systems with only one antenna. In high density networks the packet-in-packet resynchronization further improves the communication reliability.

Ultra-Low Power Consumption

The QPG6100's advanced integrated energy management system allows it to operate from a standard lithium coin cell battery, with a minimum of additional components. It includes ultra-low power voltage level detectors and overvoltage protection circuitry, allowing safe operation and graceful shutdown. The battery lifetime monitor tracks the usage of the battery and provides an early exhaustion warning. The

intelligent sensor hub allows for quick and low power measurements during standby. The integrated DC/DC Buck converter can be used to further lower the power consumption in active mode, at the cost of two external components.

General Characteristics

Package	QFN40, 6x6 mm
Operating Temperature	-40 to +125 °C
Storage Temperature	-50 to +150 °C
Soldering Temperature	260 °C (10 s max)
Compliance	RoHS

Electrical Characteristics

Standby Mode Currents ¹

Using internal LjRC oscillator	0.9 µA
Using 32KHz crystal oscillator (optional)	1.5 µA
Using 32MHz crystal oscillator	850 µA

Operational Currents ¹ (with / without DC/DC Converter)

Receive IEEE 802.15.4, single antenna	3.9 / 5.5 mA
Receive IEEE 802.15.4, antenna diversity	5.0 / 7.2 mA
Receive Bluetooth (1 Mbit/s)	7 / 10.2 mA
Transmit (at 0 dBm)	11.1 / 16.8 mA
Transmit (at 7 dBm, low power mode)	18.8 / 27.1 mA
Transmit (at 10 dBm)	24 / 37 mA

Supply Voltage	1.8 to 3.6 V
----------------	--------------

Interfaces and Peripherals

Programmable GPIO lines	up to 31
Analog input lines	up to 6
Keyboard (HW assisted)	max 8 x 8
8-bit PWM with fading support	4 outputs
16-bit PWM engine	8 outputs
UART interfaces	3 (one for SW debug)
SPI and I ² C Master and Slave peripheral interfaces	
I ² S Master/Slave interface for digital audio devices	
USB 2.0 Device interface	
PDM Microphone interface	
10/12-bit ADC to monitor the analog input lines, the power supply level and the temperature	
Low power comparator	
High speed programming interface	

Crystal Frequency	32.000 MHz (±40 ppm)
Optional	32.768 kHz

Radio Characteristics

Radio Regulations compliant	ETSI EN 300 328 FCC CFR-47 Part 15 ARIB STD-T66
Transmit Power	
Low power mode	+7 dBm
High power mode	+10 dBm (adjustable down in 1 dB steps)

IEEE 802.15.4 Radio Characteristics

Standards compliant	IEEE 802.15.4-2015
Frequency Band	2400 – 2483.5 MHz
Channels	16 (programmable, 5 MHz steps)
Data Rate	250 kbit/s
Receiver Sensitivity ¹	-101 dBm typical
Antenna diversity gain ²	8 dB (increases the 'effective' receiver sensitivity to -110 dBm)

Bluetooth Low Energy Radio Characteristics

Standards compliant	Bluetooth Core Specification v 5.1, Low Energy
Frequency Band	2402 – 2480 MHz
Channels	40 (2 MHz step size)
Data Rate	125 kbit/s, 500 kbit/s, 1 Mbit/s, 2 Mbit/s
Receiver Sensitivity ¹	(typical)
2 Mbit/s	-95 dBm
1 Mbit/s	-98 dBm
500 kbit/s	-101 dBm
125 kbit/s	-105 dBm

1) Typical, at 3.0 V and 25 °C, unless specified otherwise.

2) For typical indoor usage in an environment with 50 ns delay spread and 2 MHz signal bandwidth using the Rayleigh fading model: antenna diversity with 2 antennas results in a 8 dB improved link budget at a 1% outage probability compared to no antenna diversity. The 8 dB in link budget translates into 70% more range, if using a two-slope range model with the breakpoint at 10 m and $g_1 = 2$, $g_2 = 3.5$.

Reference Designs, Tools and SW

Qorvo reference designs, development kits, software libraries and production platforms provide a quick time-to-market solution for sensor and control devices for Smart Home networks and for other IEEE 802.15.4 / Bluetooth Low Energy communication products.

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: lpw.support@qorvo.com

Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2018 - 2021 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc. | ConcurrentConnect™ technology is a trademark of Qorvo, Inc.

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Qorvo is under license. Arm and Cortex are registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere. All other trademarks and trade names are those of their respective owners.